



# Centurion™ C2-S

## Two Cylinder Semi Automatic Gas Cabinet



**SEMI-GAS®** supplies SEMI S2 certified, production-ready ultra high purity gas source systems, distribution systems and control technology to leaders in the Semiconductor industry and related high-tech fields. Built to address the most rigorous precision and purity demands of these specialized applications, SEMI-GAS® solutions are globally renowned for their premier levels of safety, quality, and performance.

### DESIGN STANDARDS

- ◆ Conforms to SEMI S2 Standards
- ◆ UL Labeled
- ◆ Conforms to Uniform Building and Fire Codes
- ◆ Upholds Sample Validation Testing Standards
- ◆ Helium Leak Tested to  $1 \times 10^{-9}$  atm-cm<sup>3</sup>/sec
- ◆ Equipped with GigaGuard™ ESS Controller

### FEATURES

- ◆ Safely Dispenses Hazardous Process Gases
- ◆ Automatic Shutdown in the Event of an Alarm Trip
- ◆ Utilizes Manual Purge Process
- ◆ Monitors Flow, Pressure, Exhaust and Fire Sensors
- ◆ Intuitive Operating Interface and Control
- ◆ LED Lights Provide Constant Systems Status
- ◆ Continuously Monitors System Conditions for Alarms
- ◆ Remote Outputs for System Status and/or Shutdown

### ENGINEERING DATA

- ◆ Dimensions: 86" T X 25" W X 23" D
- ◆ Exhaust Duct: 6" Diameter
- ◆ Window Open Duct Flow: 350 SCFM
- ◆ Voltage: 110 to 240 VAC, 1 Phase
- ◆ Frequency: 50 to 60 Hz

### MATERIALS OF CONSTRUCTION

- ◆ Welded 11 Ga Steel Enclosure
- ◆ Self-Closing and Self-Latching Door
- ◆ Self-Closing and Self-Latching Window
- ◆ Heavy Cast Aluminum Cylinder Brackets
- ◆ Polycarbonate Face Shield
- ◆ Durable, Corrosion Proof, Non-Skid Floor Mat
- ◆ UL Approved Fire Sprinkler
- ◆ 1/4" Thick Safety Glass Window



### ORDERING INFORMATION

Contact your SEMI-GAS® sales rep or visit [www.semi-gas.com](http://www.semi-gas.com)

### BY APPLIED ENERGY SYSTEMS

180 Quaker Lane  
Malvern, PA 19355

Phone: 610.647.8744

Fax: 610.640.4548

Email: [sales@semi-gas.com](mailto:sales@semi-gas.com)

CENTURION-C2-S-082016-V1

### SAFETY FEATURES

- ◆ **Door Switch Monitor** for applications that require extra security and/or limited access (optional)
- ◆ **Rate of Rise Heat Detector** for flammable gas applications (optional)
- ◆ **Hazardous Gas Detector** for all hazardous, toxic, and/or flammable gas applications (required for silane, consult local codes for all other gases)
- ◆ **Purge Gas Bleed Valve** for manifolds and piping systems with large internal volumes or line lengths (optional)
- ◆ **Controller Z-Purge Kit** for systems installed in Class 1 Division 2 hazardous locations, as well as applications for silane and silane mixtures greater than 1.37% (required for silane)
- ◆ **Dual Cylinder Restraints** for applications that require additional cylinder security or are located in seismic zones (required for specific seismic areas)
- ◆ **Shutboy Software Upgrade** to accommodate Shutboy valve shutters for automatically closing the gas cylinder valve during emergency situations (optional)

### ORDERING INFORMATION

Example: Two Cylinder Semi Automatic Autoswitchover Gas Cabinet



#### Product

C = Centurion™ Gas Cabinet

#### Configuration

- 1 = 1 Cylinder
- 2 = 2 Cylinder
- 3 = 3 Cylinder

#### Control

- M = Manual
- S = Semi Automatic
- A = Fully Automatic

#### Process Manifold

- 2 = 2-Valve (for inert gases)
- 3 = 3-Valve (for inert gases)
- 5 = 5-Valve (for toxic, flammable, and reactive gases)

#### Operation

- X = Autoswitchover
- N = Independent Processes

#### Purge

- P = Purge
- O = No Purge

#### Option

- I = Individual Process Cabinets
- S = System Upgrades for Silane

\*All Centurion™ Gas Cabinets can be customized to meet unique specifications. Contact your SEMI-GAS® sales rep for details.

